

Eaton definite purpose starter

A27CGD15B006

UPC:786685458243

Dimensions:

- **Height:** 7.38 IN
- **Length:** 5.81 IN
- **Width:** 5.63 IN

Weight:3.11 LB



Specifications:

- **Model:** Starter
- **Amperage Rating:** 15A
- **Coil:** Coil: 208-240 V, 50/60 Hz
- **Control Characteristics:** Common control wiring
- **Enclosure:** NEMA Type 1 Enclosed
- **Inductive Full Load:** 15 A IFL
- **Overload Range:** 4-6A
- **Phase:** Three-phase
- **Terminals:** Screw/pressure plate and quick connect terminals (side-by-side)
- **Type:** Non-reversing
- **Overload Relay:** 4-6 FLA

Supporting documents:

- [Eaton Specification Sheet - A27CGD15B006](#)

Certifications:

- CSA Certified
- UL Recognized

Product compliance: No Data