

Eaton definite purpose starter

A27CGE30B010

UPC:782116911370

Dimensions:

- **Height:** 10.17 IN
- **Length:** 5.81 IN
- **Width:** 5.63 IN

Weight:4.8 LB



Specifications:

- **Model:** Starter
- **Amperage Rating:** 30A
- **Coil:** Coil: 208-240 V, 50/60 Hz
- **Control Characteristics:** Common control wiring
- **Enclosure:** NEMA Type 1 Enclosed
- **Inductive Full Load:** 30 A IFL
- **Overload Range:** 6-10A
- **Phase:** Three-phase
- **Terminals:** Box lugs (posidrive setscrew)
- **Type:** Non-reversing
- **Overload Relay:** 6-10 FLA

Supporting documents:

- [Eaton's Volume 5-Motor Control and Protection](#)
- [Eaton Specification Sheet - A27CGE30B010](#)

Certifications:

- UL Recognized
- CSA Certified

Product compliance: No Data