

Eaton definite purpose starter

A27CGF45B057

UPC:786685291468

Dimensions:

- **Height:** 13.27 IN
- **Length:** 6.67 IN
- **Width:** 7.64 IN

Weight:10.6 LB



Specifications:

- **Model:** Starter
- **Amperage Rating:** 45A
- **Coil:** Coil: 208-240 V, 50/60 Hz
- **Control Characteristics:** Common control wiring
- **Enclosure:** NEMA Type 1 Enclosed
- **Inductive Full Load:** 45 A IFL
- **Overload Range:** 40-57A
- **Phase:** Three-phase
- **Terminals:** Box lugs (posidrive setscrew) and quick connect terminals (side-by-side)
- **Type:** Non-reversing
- **Overload Relay:** 40-57 FLA

Supporting documents:

- [Eaton Specification Sheet - A27CGF45B057](#)

Certifications:

- CSA Certified
- UL Recognized

Product compliance: No Data