

Eaton definite purpose starter

A27CNF45B024

UPC:786685291543

Dimensions:

- **Height:** 6 IN
- **Length:** 3.9 IN
- **Width:** 2.4 IN

Weight:1.98 LB



Specifications:

- **Model:** Starter
- **Amperage Rating:** 45A
- **Coil:** Coil: 208-240 V, 50/60 Hz
- **Control Characteristics:** Common control wiring
- **Enclosure:** Open with metal mounting plate
- **Inductive Full Load:** 45 A IFL
- **Phase:** Three-phase
- **Terminals:** Box lugs (posidrive setscrew) and quick connect terminals (side-by-side)
- **Type:** Non-reversing
- **Overload Relay:** 16-24 FLA

Supporting documents:

- [Eaton Specification Sheet - A27CNF45B024](#)

Certifications:

- UL Recognized
- CSA Certified

Product compliance: No Data