

Eaton definite purpose starter

A27CRE301T024

UPC:786685292083

Dimensions:

- **Height:** 5.7 IN
- **Length:** 3.9 IN
- **Width:** 2.23 IN

Weight:1.98 LB



Specifications:

- **Model:** Starter
- **Amperage Rating:** 30A
- **Coil:** Coil: 24 V, 50/60 Hz
- **Control Characteristics:** Common control wiring
- **Enclosure:** Open with DIN rail mounting adapter
- **Inductive Full Load:** 30 A IFL
- **Phase:** Three-phase
- **Terminals:** Box lugs (posidrive setscrew)
- **Type:** Non-reversing
- **Overload Relay:** 16-24 FLA

Supporting documents:

- [Eaton's Volume 5-Motor Control and Protection](#)
- [Eaton Specification Sheet - A27CRE301T024](#)

Certifications:

- CSA Certified
- UL Recognized

Product compliance: No Data