

## Eaton definite purpose starter

**A27SGC15A006**

**UPC:**782116913695

### **Dimensions:**

- **Height:** 5.5 IN
- **Length:** 3.7 IN
- **Width:** 2.4 IN

**Weight:**1.6 LB



### **Specifications:**

- **Model:** Starter
- **Amperage Rating:** 15A
- **Coil:** Coil: 110-120 V, 50/60 Hz
- **Control Characteristics:** Separate control wiring
- **Enclosure:** NEMA Type 1 Enclosed
- **Inductive Full Load:** 15 A IFL
- **Overload Range:** 4-6A
- **Phase:** Three-phase
- **Terminals:** Screw/pressure plate
- **Type:** Non-reversing
- **Overload Relay:** 4-6 FLA

### **Supporting documents:**

- [Eaton's Volume 5-Motor Control and Protection](#)
- [Eaton Specification Sheet - A27SGC15A006](#)

### **Certifications:**

- CSA Certified
- UL Recognized

**Product compliance:** No Data