

## Eaton definite purpose starter

**B27CGD25B024**

**UPC:**786685458434

### Dimensions:

- **Height:** 10.17 IN
- **Length:** 5.81 IN
- **Width:** 5.63 IN

**Weight:**4.8 LB



### Specifications:

- **Model:** Starter
- **Amperage Rating:** 25A
- **Coil:** Coil: 208-240 V, 50/60 Hz
- **Control Characteristics:** Common control wiring
- **Enclosure:** NEMA Type 1 Enclosed
- **Inductive Full Load:** 25 A IFL
- **Overload Range:** 16-24A
- **Phase:** Single-phase
- **Terminals:** Screw/pressure plate and quick connect terminals (side-by-side)
- **Type:** Non-reversing
- **Overload Relay:** 16-24 FLA

### Supporting documents:

- [Eaton Specification Sheet - B27CGD25B024](#)

### Certifications:

- UL Recognized
- CSA Certified

**Product compliance:** No Data