

# Eaton definite purpose starter

**B27CGE40A040**

**UPC:**782116917754

## Dimensions:

- **Height:** 13.27 IN
- **Length:** 6.67 IN
- **Width:** 7.64 IN

**Weight:**10.6 LB



## Specifications:

- **Model:** Starter
- **Amperage Rating:** 40A
- **Coil:** Coil: 110-120 V, 50/60 Hz
- **Control Characteristics:** Common control wiring
- **Enclosure:** NEMA Type 1 Enclosed
- **Inductive Full Load:** 40 A IFL
- **Overload Range:** 24-40A
- **Phase:** Single-phase
- **Terminals:** Box lugs (posidrive setscrew)
- **Type:** Non-reversing
- **Overload Relay:** 24-40 FLA

## Supporting documents:

- [Eaton's Volume 5-Motor Control and Protection](#)
- [Eaton Specification Sheet - B27CGE40A040](#)

## Certifications:

- UL Recognized
- CSA Certified

**Product compliance:** No Data