

## Eaton definite purpose starter

**B27SGC25T010**

**UPC:**782116920952

### Dimensions:

- **Height:** 10.17 IN
- **Length:** 5.81 IN
- **Width:** 5.63 IN

**Weight:**4.8 LB



### Specifications:

- **Model:** Starter
- **Amperage Rating:** 25A
- **Coil:** Coil: 24 V, 50/60 Hz
- **Control Characteristics:** Separate control wiring
- **Enclosure:** NEMA Type 1 Enclosed
- **Inductive Full Load:** 25 A IFL
- **Overload Range:** 6-10A
- **Phase:** Single-phase
- **Terminals:** Screw/pressure plate
- **Type:** Non-reversing
- **Overload Relay:** 6-10 FLA

### Supporting documents:

- [Eaton's Volume 5-Motor Control and Protection](#)
- [Eaton Specification Sheet - B27SGC25T010](#)

### Certifications:

- UL Recognized
- CSA Certified

**Product compliance:** No Data