

# Eaton definite purpose starter

**B27SGE30B010**

**UPC:**782116921362

**Dimensions:**

- **Height:** 10.17 IN
- **Length:** 5.81 IN
- **Width:** 5.63 IN

**Weight:**4.8 LB



**Specifications:**

- **Model:** Starter
- **Amperage Rating:** 30A
- **Coil:** Coil: 208-240 V, 50/60 Hz
- **Control Characteristics:** Separate control wiring
- **Enclosure:** NEMA Type 1 Enclosed
- **Inductive Full Load:** 30 A IFL
- **Overload Range:** 6-10A
- **Phase:** Single-phase
- **Terminals:** Box lugs (posidrive setscrew)
- **Type:** Non-reversing
- **Overload Relay:** 6-10 FLA

**Supporting documents:**

- [Eaton's Volume 5-Motor Control and Protection](#)
- [Eaton Specification Sheet - B27SGE30B010](#)

**Certifications:**

- CSA Certified
- UL Recognized

**Product compliance:** No Data