

## Eaton QB GFCI circuit breaker

**QBGFT1015V**

**UPC:**786679139813

**Dimensions:**

- **Height:** 1.2 IN
- **Length:** 5.1 IN
- **Width:** 3.3 IN

**Weight:**.4 LB

**Notes:**HACR rated

**Warranties:**

- 1 year

**Specifications:**

- **Type:** Ground fault circuit breaker
- **Special Features:** 50 Degrees
- **Amperage Rating:** 15A
- **Interrupt Rating:** 10 kAIC
- **Number Of Poles:** Single-pole
- **Voltage Rating:** 120/240V
- **Trip Type:** Non-Interchangeable
- **Trip Setting Amperage:** 5 mA Trip sensitivity
- **Wire Size:** #14-10 AWG Cu or #12-10 AWG Al
- **Circuit Breaker Type:** QBGF

**Supporting documents:**

- [Loadcenters and Circuit Breakers](#)
- [Eaton Specification Sheet - QBGFT1015V](#)

**Certifications:**

- UL 489

**Product compliance:** No Data

