

Eaton QB GFCI circuit breaker

QBGFT2040

UPC:786676026741

Dimensions:

- **Height:** 2 IN
- **Length:** 4.5 IN
- **Width:** 2.75 IN

Weight:.6 LB

Notes:HACR rated

Warranties:

- 1 year

Specifications:

- **Type:** Ground fault circuit breaker
- **Special Features:** 5 mA Trip Sensitivity
- **Amperage Rating:** 40A
- **Interrupt Rating:** 10 kAIC
- **Number Of Poles:** Two-pole
- **Voltage Rating:** 120/240V
- **Trip Type:** Common trip
- **Trip Setting Amperage:** 5 mA Trip sensitivity
- **Wire Size:** #8 Cu, #8–6 Al
- **Circuit Breaker Type:** QBGF

Supporting documents:

- [Loadcenters and Circuit Breakers](#)
- [Eaton Specification Sheet - QBGFT2040](#)

Certifications:

- UL 489

Product compliance: No Data