

Standard Part Numbers

Parts No.	Voltage	Duty Cycle	Power	Resistance (Ohms)	Operation	Typical Force (oz). 100% Voltage, 77° F, Stroke @				
						0.000"	0.125"	0.250"	0.500"	0.750"
53800-86*	6 VDC	Intermittent	12 Watts	3	Pull	109	47.1	31	14.3	0
53800-87*	12 VDC			12						
53800-88*	24 VDC			48						
53800-92	6 VDC	Pulse	48 Watts	0.75		109	71.2	46.8	19.4	0
53800-93	12 VDC			3						
53800-94	24 VDC			12						

(*) Normally Stocked

Non stocked items require a minimum order