

Standard Part Numbers

Parts No.	Voltage	Duty Cycle	Power	Resistance (Ohms)	Operation	Typical Force (oz). 100% Voltage, 77°, Stroke @				
						0.000"	0.125"	0.250"	0.500"	0.750"
53795-80	6 VDC	Continuous	14 Watts	2.57	Pull	200	100	52	25	17
53796-80	6 VDC			2.57	Push					
53795-81*	12 VDC			10.3	Pull					
53796-81	12 VDC			10.3	Push					
53795-82*	24 VDC			41.1	Pull					
53796-82	24 VDC			41.1	Push					
53795-83	110 VDC			864	Pull					
53796-83	110 VDC			864	Push					
53795-84	6 VDC	Intermittent	40 Watts	0.9	Pull	265	175	120	63	35
53796-84	6 VDC			0.9	Push					
53795-85*	12 VDC			3.6	Pull					
53796-85	12 VDC			3.6	Push					
53795-86*	24 VDC			14.4	Pull					
53796-86	24 VDC			14.4	Push					
53795-87	110 VDC			302.5	Pull					
53796-87	110 VDC			302.5	Push					
53795-88	12 VDC	Pulse	140 Watts	1.03	Pull	328	262	210	140	85
53796-88	12 VDC			1.03	Push					
53795-89	24 VDC			4.11	Pull					
53796-89	24 VDC			4.11	Push					
53795-90	110 VDC			86.4	Pull					
53796-90	110 VDC			86.4	Push					

(*) Normally Stocked

Non stocked items require a minimum order