



STAINLESS STEEL ENCLOSURE

Wall Mounted, NEMA 4X, UL Approved



The **SERIES SSE** Stainless Steel Enclosures are wall mounted enclosures designed to house electrical controls, instruments, and components in locations that are wet, oily, or may be regularly hosed down. These units are made of 304 SS, NEMA 4X outdoor environment rated and carry a UL approval.

FEATURES/BENEFITS

- Concealed hinges that allow 180° of rotation for easy instrumentation access
- Quarter turn latch can easily opened or closed with a screwdriver
- Included ground studs on the door and body for easy electrical grounding
- Standoffs that provide easy installation of optional sub-panels
- Mounting holes included on the back of the enclosure allow for versatile mounting and standoffs provide easy installation of optional sub-panels
- Oil-resistant gasket, sealing washers, and hole plugs that ensure that the components are protected at all times
- Optional sub-panels and drip shields can be purchased separately for added protection
- Mounting feet are included with the SSE-J but must be purchased separately for the SSE-E enclosures

SPECIFICATIONS

Materials: Enclosure: 304 SS; Mounting feet: 316 SS†; Hinges: Plastic; All other components: Carbon steel.
Rating: NEMA 4X (IP66).
Dimensions: See chart.
Thickness: 0.048" (1.22 mm) for A-SSE-D-XX; 0.063" (1.60 mm) for SSE-J-XXXXXX; 0.075" (1.91 mm) for SSE-E-XXXXXX and A-SSE-PJ-XXXX; 0.088" (2.24 mm) for A-SSE-P-XXXX; 0.13" (3.30 mm) for A-SSE-F.
Weight: See chart.
Agency Approvals: CSA, cULus. (Meets the technical requirements of EU Directive 2011/65/EU (RoHS II).
 †Included with SSE-J models only.

APPLICATIONS

- Outdoor applications
- Water Production
- Wastewater Process
- Housing general controls and gages
- Securing instrumentation and avoiding tampering

MODEL CHART											
Enclosure** Model*	Height in (cm)	Width in (cm)	Depth in (cm)	Weight lb (kg)	Sub-Panel Model	Height in (cm)	Width in (cm)	Weight lb (kg)	Drip Shield Model	Width in (cm)	Weight lb (kg)
SSE-J-100804	10 (25)	8 (20)	4 (10)	6 (2.7)	A-SSE-PJ-1008	9 (23)	7 (18)	4 (1.8)	A-SSE-D-12	12 (30)	3 (1.4)
SSE-J-121006	12 (30)	10 (25)	6 (15)	10 (4.5)	A-SSE-PJ-1210	11 (29)	9 (23)	2 (0.9)	A-SSE-D-16	16 (41)	4 (1.8)
SSE-J-121206	12 (30)	12 (30)	6 (15)	11 (5)	A-SSE-PJ-1212	11 (29)	11 (29)	3 (1.4)	A-SSE-D-20	20 (51)	4 (1.8)
SSE-J-141206	14 (36)	12 (30)	6 (15)	13 (5.9)	A-SSE-PJ-1412	13 (34)	11 (29)	3 (1.4)	A-SSE-D-24	24 (61)	5 (2.3)
SSE-J-161406	16 (41)	14 (36)	6 (15)	16 (7.3)	A-SSE-PJ-1614	15 (39)	13 (34)	3 (1.4)	A-SSE-D-30	30 (76)	4 (1.8)
SSE-E-161606	16 (41)	16 (41)	6 (15)	21 (10)	A-SSE-P-1616	13 (33)	13 (33)	6 (2.7)			
SSE-E-201606	20 (51)	16 (41)	6 (15)	28 (13)	A-SSE-P-2016	17 (43)	13 (33)	8 (3.6)			
SSE-E-202006	20 (51)	20 (51)	6 (15)	34 (15)	A-SSE-P-2020	17 (43)	17 (43)	10 (4.5)			
SSE-E-202408	20 (51)	24 (61)	8 (20)	43 (20)	A-SSE-P-2416	21 (53)	13 (33)	14 (6.4)			
SSE-E-241608	24 (61)	16 (41)	8 (20)	36 (16)	A-SSE-P-2420	21 (53)	17 (43)	11 (5)			
SSE-E-242006	24 (61)	20 (51)	6 (15)	40 (18)	A-SSE-P-2424	21 (53)	21 (53)	17 (7.7)			
SSE-E-242408	24 (61)	24 (61)	8 (20)	49 (22)	A-SSE-P-3016	27 (69)	13 (33)	14 (6.4)			
SSE-E-301606	30 (76)	16 (41)	6 (15)	41 (19)	A-SSE-P-3020	27 (69)	17 (43)	18 (8.2)			
SSE-E-302008	30 (76)	20 (51)	8 (20)	52 (24)	A-SSE-P-3024	27 (69)	21 (53)	22 (10)			
SSE-E-302408	30 (76)	24 (61)	8 (20)	53 (24)	A-SSE-P-3030	27 (69)	27 (69)	28 (13)			
SSE-E-303008	30 (76)	30 (76)	8 (20)	67 (30)							

*For additional sizes contact factory. **For 316 SS enclosures contact factory.

ACCESSORIES	
Model	Description
A-CSE-L	Keylocking wing knob door latch, includes 1 lock and 2 keys
A-CSE-K	Replacement keys, includes 2 keys
A-SSE-F	Mounting feet, includes 4 feet†

†Included with SSE-J models only.

