

Eaton EXH5 480360 300

Catalog Number: EXH5 480360 300

Eaton Crouse-Hinds series EXH electric air heater, 60 Hz, 102,360 BTU/hr, 30 kW, Steel, 36.1A max., Three-phase, 26.4°F (14.6°C) temperature rise, 480 Vac

General specifications



Photo is representative

Product Name	Catalog Number
Eaton Crouse-Hinds series EXH electric air heater	EXH5 480360 300
	UPC
	662276647497
Product Length/Depth	Product Height
27.44 in	26.5 in
Product Width	Product Weight
22.63 in	201 lb

Certifications and compliances

Area classification

Hazardous/Classified Locations

Standards type

NEC/CEC

NEC hazardous rating

Class I, Division 1

Class II, Division 1

Class II, Division 2

Class I, Division 2

NEMA Rating

9

7

Product specifications

Voltage rating

480 Vac

Phase

Three-phase

Frequency rating

60 Hz

Power output

30 kW

Maximum total amperage

36.1 A

Heat output

102,360 BTU/hr

Temperature rise

26.4°F (14.6°C)

Material

Steel

Resources

Catalogs

[EXH Series Explosionproof Electric Heater catalog page](#)

Certification reports

[EXH Explosionproof Electric Heaters Canadian certification](#)

[EXH Explosionproof Electric Heaters UL certification](#)

Installation instructions

[IF 11592 - EXH5 Series Explosionproof Electric Heater](#)

Specifications and datasheets

[Eaton Specification Sheet - EXH5 480360 300](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)