

Eaton 10063PMURF

Catalog Number: 10063PMURF

Eaton LV Unipak capacitor bank, UNIPAK, Low Voltage Fixed Capacitor Banks, 98A, 600V, Three-phase, 100 kVAR, Protected, Neon red blown-fuse indicating lights, Three slottedblade-type fuses, C1 Frame



General specifications

Product Name	Catalog Number
Eaton LV Unipak capacitor bank	10063PMURF
UPC	Product Length/Depth
782116059324	10.6 in
Product Height	Product Width
26.3 in	12.1 in
Product Weight	Warranty
69 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
Certifications	Catalog Notes
CSA Certified UL Listed	Multiply the 240V kVAR rating by 0.75 to calculate the kVAR value at 208V.

defaultTaxonomyAttributeLabel

Type

UNIPAK

Amperage Rating

98A

Fuse type

Three slottedblade type fuses with 200,000 ampere interrupting capacity, Fuses mounted on stand-off bushings or fuse blocks, solderless connectors for easy hookup of incoming line conductors.

Phase

Three-phase

Product Category

Low Voltage Fixed Capacitor Banks

Voltage rating

600 V

Enclosure

NEMA 1, NEMA 3R

Enclosure material

14 gauge steel finished with durable powder coat finish

Frame size

C1

Indicators

Red, neon blown-fuse indicating lights are protected by transparent weatherproof guard

Protection

Three fuses, three lights

Rating

100 kVAR

Resources

Catalogs

[Eaton's Volume 3—Power Distribution and Control Assemblies](#)

Specifications and datasheets

[Eaton Specification Sheet - 10063PMURF](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)