

# Eaton 1107W-10-L

Catalog Number: 1107W-10-L

Eaton residential grade duplex receptacle, 10-pack, , #14-10 AWG, 15A, Flush, 125V, White, Brass, Impact-resistant thermoplastic, 5-15R, Two-pole, Three-wire, Screw, Thermoplastic

## General specifications

Product Name	Catalog Number
Eaton residential grade decorator duplex receptacle	1107W-10-L
	UPC 032664749636
Product Length/Depth	Product Height
1.3 in	3.81 in
Product Width	Product Weight
0.69 in	1.31 lb
Compliances	Certifications
RoHS Compliant NAFTA	NOM Federal Specification Classification 6233 01 UL



## defaultTaxonomyAttributeLabel

### Device type

Receptacle

### Amperage Rating

15A

### Voltage rating

125V

### Contact material

Brass

### Features

10-pack

### Application

Residential

### Device grade

Standard grade

### Wiring method

Side and push

### Environmental conditions

Indoor

### Number of wires

Three-wire

### Mounting method

Flush

### Number Of Poles

Two-pole

### Style type

Decorator

### Material

Thermoplastic

### Color

White

### Connection type

Screw

### Allowable wire size

#14-10 AWG

### NEMA configuration

## Resources

### Multimedia

[Residential straight blade receptacles](#)

### Specifications and datasheets

[Eaton Specification Sheet - 1107W-10-L](#)

5-15R

Torque rating

14 lbf-inch

Design type

Straight blade

Face/body material

Impact-resistant thermoplastic

Receptacle type

Duplex



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)