

# Eaton 1163A-210

Catalog Number: 1163A-210

Eaton 60 Series Photoelectric Sensor Head, Photoelectric, 1.25 diameter, Forward Viewing, Sensor distance: 159 Ft., Stainless Steel enclosure, 12 Vdc input, Thu-Beam, 9 Ft. ( 2.7m )

## General specifications



|                                      |                      |
|--------------------------------------|----------------------|
| Product Name                         | Catalog Number       |
| Eaton 60 series photoelectric sensor | 1163A-210            |
| UPC                                  | Product Length/Depth |
| 782113819624                         | 1.13 in              |
| Product Height                       | Product Width        |
| 4 in                                 | 1.13 in              |
| Product Weight                       | Warranty             |
| 0.5 lb                               | 3 year               |
| Compliances                          |                      |
| Contact Manufacturer                 |                      |

**Cable type**

Polyvinyl Chloride (PVC)

**Enclosure material**

Stainless steel

**Operating mode**

Thru-beam

**Sensor type**

Through beam

**Switch type**

Photoelectric

**Input voltage**

12 Vdc

**Cord length**

108 ft

**Operating temperature - max**

158 °F

**Operating temperature - min**

-40 °F

**Environmental rating**

NEMA 3, NEMA 4, NEMA 6, NEMA 12, NEMA 13

**Specifications and datasheets**[Eaton Specification Sheet - 1163A-210](#)

Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)