

Eaton 2355-BOX

Catalog Number: 2355-BOX

Eaton safety grip locking connector, Stand-alone box packaging, #14-8 AWG, 20A, Commercial, 125/250V, Back wiring, Yellow, L10-20, Three-pole, Three-wire, Nylon, .25 to .75 in



Photo is representative

General specifications

Product Name	Catalog Number
Eaton Arrow Hart standard locking connector	2355-BOX
	UPC
	032664323003
Product Length/Depth	Product Height
9.5 in	2.56 in
Product Width	Product Weight
3.75 in	0.25 lb
Certifications	
UL Listed	
NOM	
CSA certified	

defaultTaxonomyAttributeLabel

Special features

Armored

Type

Locking connector

Amperage Rating

20A

Voltage rating

125/250 V

Contact material

Brass

Application

Commercial

Device grade

Commercial

Wiring method

Back

Number of wires

3

Non-grounding

Number Of Poles

Three-pole

Color

Yellow

Cord diameter

0.25-0.63 in (6.4-16.8 mm)

Material

Nylon

Operating temperature

-20 to 60 °C (-4 to 140 °F)

Allowable wire size

#14-8 AWG

NEMA configuration

L10-20

Torque rating

15 lbf-inch

Resources

Brochures

[Wiring Devices Buyer's Guide](#)

Multimedia

[Arrow Hart - Connecting Safety to Reliability since 1890](#)

Specifications and datasheets

[Eaton Specification Sheet - 2355-BOX](#)

Design type

Armored

Face/body material

Polypropylene



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)