

Eaton 2493-BOX

Catalog Number: 2493-BOX

Eaton Arrow Hart standard locking connector, Stand-alone box packaging, 15A, Commercial, 125V, Yellow, Two-pole, Three-wire

General specifications



Photo is representative

Product Name	Catalog Number
Eaton Arrow Hart standard locking connector	2493-BOX
	UPC
	032664324901
Product Length/Depth	Product Height
1.35 in	2.37 in
Product Width	Product Weight
1.5 in	0.181 lb
Certifications	
cULus Listed	
NOM	
CSA certified	

[Special features](#)

Armored

[Type](#)

Locking connector

[Amperage Rating](#)

15A

[Voltage rating](#)

125 V

[Contact material](#)

Brass

[Application](#)

Commercial

[Device grade](#)

Commercial

[Wiring method](#)

Back

[Number of wires](#)

3

Grounding

[Number Of Poles](#)

Two-pole

[Color](#)

Yellow

[Cord diameter](#)

0.25-0.63 in (6.4-16.8 mm)

[Material](#)

Nylon

[Operating temperature](#)

-20 to 60 °C (-4 to 140 °F)

[Allowable wire size](#)

#14-8 AWG

[NEMA configuration](#)

L5-15

[Torque rating](#)

15 lbf-inch

[Brochures](#)

[Wiring Devices Buyer's Guide](#)

[Multimedia](#)

[Arrow Hart - Connecting Safety to Reliability since 1890](#)

[Specifications and datasheets](#)

[Eaton Specification Sheet - 2493-BOX](#)

Design type

Armored

Face/body material

Polypropylene



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.
All other trademarks are property of their respective owners.



Eaton.com/socialmedia