

# Eaton 302410 RHC

Catalog Number: 302410 RHC

Eaton B-Line series Type 3/3R panel enclosures, 30" height, 10" length, 24" width, NEMA 3R, Hinged cover, RHC enclosure, Wall mount, Medium single door, External mounting feet, Carbon steel



Photo is representative

## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton B-Line series Type 3/3R panel enclosures	302410 RHC
	UPC
	799038505334
<b>Product Length/Depth</b>	<b>Product Height</b>
10 in	30 in
<b>Product Width</b>	<b>Product Weight</b>
24 in	68.7 lb
<b>Certifications</b>	
UL 50	
CSA C22.2.	
NEMA	

## Material/finish

### Material

Carbon steel

### Wall thickness

14 gauge

### Finish color

Painted

### Color

ANSI 61 gray

## Model

### Style

Medium single door

### Model

RHC enclosure

### Cover type

Hinged

### Mounting method

Wall

### Mounting hole details

External mounting feet

### Locking provisions

Padlock provision

### Closure type

Hinged

### Special features

Rain hood,plated screws,piano hinge with s.s. pin

## Standards

### NEMA Rating

3R

### Country of origin

US

## Resources

### Catalogs

[Type1-3-3r-enclosure-catalog-section](#)

### Specifications and datasheets

[Eaton Specification Sheet - 302410 RHC](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)