

Eaton 302420-SDWLG

Catalog Number: 302420-SDWLG

Eaton B-Line series wall mounted panel enclosure,30" height,20" length,24" width,NEMA 4,Hinged cover,SDWLG enclosure,Wall mount,Medium single door,Thru holes,optional external mounting feet,Carbon steel,Seamless poured in-place gasket

General specifications



Photo is representative

Product Name	Catalog Number
Eaton B-Line series wall mounted panel enclosure	302420-SDWLG
	UPC
	799038545996

Product Length/Depth	Product Height
20 in	30 in

Product Width	Product Weight
24 in	74.2 lb

Certifications

UL 50
CSA C22.2.
NEMA

defaultTaxonomyAttributeLabel

Country of origin

US

Special features

1/4 turn latches

Style

Medium single door

Finish color

Painted

Color

RAL 7035 light gray

NEMA Rating

4

Cover type

Hinged

Wall thickness

16 gauge, 14 gauge

Material

Carbon steel

Model

SDWLG enclosure

Mounting method

Wall

Closure type

Hinged

Mounting hole details

Thru holes, optional external mounting feet

Resources

Catalogs

[Disconnect Enclosure Catalog](#)

Specifications and datasheets

[Eaton Specification Sheet - 302420-SDWLG](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)