

Eaton 30308 RHC

Catalog Number: 30308 RHC

Eaton B-Line series Type 3/3R panel enclosures, 30" height, 8" length, 30" width, NEMA 3R, Hinged cover, RHC enclosure, Wall mount, Medium single door, External mounting feet, Carbon steel



Photo is representative

General specifications

Product Name	Catalog Number
Eaton B-Line series Type 3/3R panel enclosures	30308 RHC
	UPC
	799038505341
Product Length/Depth	Product Height
8 in	30 in
Product Width	Product Weight
30 in	78 lb
Certifications	
UL 50	
CSA C22.2.	
NEMA	

Material/finish

Material

Carbon steel

Wall thickness

14 gauge

Finish color

Painted

Color

ANSI 61 gray

Model

Style

Medium single door

Model

RHC enclosure

Cover type

Hinged

Mounting method

Wall

Mounting hole details

External mounting feet

Locking provisions

Padlock provision

Closure type

Hinged

Special features

Rain hood,plated screws,piano hinge with s.s. pin

Standards

NEMA Rating

3R

Country of origin

US

Resources

Catalogs

[Type1-3-3r-enclosure-catalog-section](#)

Specifications and datasheets

[Eaton Specification Sheet - 30308 RHC](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)