

Eaton 3524BK

Catalog Number: 3524BK

Eaton locking flanged inlet, 10A, 20A, Industrial, 250/600V, Black, Non-NEMA, Four-pole, Five-wire, grounding, Polycarbonate

General specifications



Product Name	Catalog Number
Eaton Arrow Hart locking flanged inlet	3524BK
UPC	Product Length/Depth
040893674155	3.75 in
Product Height	Product Width
2.38 in	2.94 in
Product Weight	Compliances
0.297 lb	RoHS Compliant
Certifications	
cULus Listed	

defaultTaxonomyAttributeLabel

Special features

Watertight locking receptacle

Type

Locking flanged inlet

Amperage Rating

10A, 20A

Voltage rating

600/250V

Contact material

Brass

Application

Industrial

Device grade

Extra heavy-duty industrial specification grade

Wiring method

Back

Number of wires

5

Grounding

Number Of Poles

Four-pole

Color

Black

Material

Nylon

Operating temperature

-40 to 75 °C (-40 to 167 °F)

NEMA configuration

Non-NEMA

Design type

Flanged inlet

Face/body material

Nylon

Resources

Catalogs

[Arrow Hart Buyers Guide Section C](#)

Multimedia

[Arrow Hart - Connecting Safety to Reliability since 1890](#)

Specifications and datasheets

[Eaton Specification Sheet - 3524BK](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)