

Eaton 3525BK

Catalog Number: 3525BK

Eaton locking flanged outlet, 10A, 20A, Industrial, 250/600V, Black, Non-NEMA, Four-pole, Five-wire, grounding, Polycarbonate

General specifications



Product Name	Catalog Number
Eaton Arrow Hart locking flanged outlet	3525BK
UPC	Product Length/Depth
040893674162	3.75 in
Product Height	Product Width
2.38 in	2.94 in
Product Weight	Compliances
0.379 lb	RoHS Compliant
Certifications	
UL Listed	
cULus Listed	

defaultTaxonomyAttributeLabel

Special features

Locking flanged inlet

Type

Locking flanged outlet

Amperage Rating

10A, 20A

Voltage rating

600/250V

Contact material

Brass

Application

Industrial

Device grade

Extra heavy-duty industrial specification grade

Wiring method

Back

Number of wires

5

Grounding

Number Of Poles

Four-pole

Color

Black

Material

Nylon

Operating temperature

-40 to 75 °C (-40 to 167 °F)

NEMA configuration

Non-NEMA

Torque rating

For #10-14 AWG: 14-16 lbf-inch. For #8 AWG: 20 lbf-inch

Design type

Flanged outlet

Face/body material

Nylon

Resources

Brochures

Wiring Devices Buyer's Guide

Multimedia

Arrow Hart - Connecting Safety to Reliability since 1890

Specifications and datasheets

Eaton Specification Sheet - 3525BK



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)