

Eaton 363010-4XSS63PT

Catalog Number: 363010-4XSS63PT

Eaton B-Line series wall mounted panel enclosure, 36" height, 10" length, 30" width, NEMA 4X, Hinged cover, 4XSS63PT enclosure, Wall mount, Medium single door, External mounting feet, 316 stainless steel, Seamless poured in-place gasket



Photo is representative

General specifications

Product Name	Catalog Number
Eaton B-Line series wall mounted panel enclosure	363010-4XSS63PT
	UPC
	782051884197
Product Length/Depth	Product Height
10 in	36 in
Product Width	Product Weight
30 in	88.5 lb
Certifications	
UL 508A	
CSA C22.2.	
NEMA	

defaultTaxonomyAttributeLabel

Country of origin

US

Special features

3-pt latching handle

Style

Medium single door

Finish color

#4 brushed

Color

Gray

NEMA Rating

4X

Cover type

Hinged

Wall thickness

14 gauge

Material

316 stainless steel

Model

4XSS63PT enclosure

Mounting method

Wall

Closure type

Hinged

Locking provisions

Key lock padlock provision

Mounting hole details

External mounting feet

Resources

Catalogs

[Disconnect Enclosure Catalog](#)

Specifications and datasheets

[Eaton Specification Sheet - 363010-4XSS63PT](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)