

Eaton 3769

Catalog Number: 3769

Eaton locking receptacle, #10-6 AWG, 50A, Industrial, 600 Vac, 250Vdc, Back wiring, Black, Single, Non-NEMA, Three-pole, Four-wire, grounding, Steel, California standard

General specifications



Product Name	Catalog Number
Eaton Arrow Hart California standard locking receptacle	3769
	UPC
	040893681665

Product Length/Depth	Product Height
3.75 in	2.38 in

Product Width	Product Weight
2.38 in	0.79 lb

Certifications

CSA certified
UL Listed
cULus Listed

defaultTaxonomyAttributeLabel

Special features

Locking flanged inlet with lid

Type

Locking receptacle

Amperage Rating

50 A

Voltage rating

600 Vac, 250 Vdc

Contact material

Zinc plated brass

Application

Industrial

Device grade

Extra heavy duty

Wiring method

Back

Number of wires

Grounding

4

Number Of Poles

Three-pole

Color

Black

Material

Steel

Operating temperature

-40 to 105 °C (-40 to 221 °F)

Standard

California standard

Allowable wire size

#10-6 AWG

NEMA configuration

Non-NEMA

Design type

Single receptacle

Resources

Brochures

[Wiring Devices Buyer's Guide](#)

Multimedia

[Arrow Hart - Connecting Safety to Reliability since 1890](#)

Specifications and datasheets

[Eaton Specification Sheet - 3769](#)

Face/body material

Glass filled nylon

Receptacle type

Locking



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)