

Eaton 4049-21BK-BU

Catalog Number: 4049-21BK-BU

Eaton panel mount/snap-in plug, #14-12 AWG, 15A, Commercial, Snap-in, Panel, 125V, Wire leads and quick connect, Black, Brass, Thermoset face and Polypropylene base, 5-15R, Single, Screw, Thermoplastic

General specifications



Product Name	Catalog Number
Eaton panel mount/snap-in plug	4049-21BK-BU
UPC	Product Length/Depth
032664594038	0.94 in
Product Height	Product Width
1.22 in	0.65 in
Product Weight	Certifications
0.07 lb	cRUus

Photo is representative

defaultTaxonomyAttributeLabel

Device type

Plug

Type

OEM

Amperage Rating

15A

Voltage rating

125V

Contact material

Brass

Features

8 quick wire ports

Application

Commercial

Device grade

Commercial specification grade

Wiring method

Wire leads and quick connect

Number of wires

3

Mounting method

Snap-in

Panel

Number Of Poles

Two-pole

Style type

Standard

Material

Thermoplastic

Color

Black

Connection type

Screw

Allowable wire size

#14-12 AWG

Resources

Catalogs

[Arrow Hart Buyers Guide A-22](#)

Multimedia

[Residential straight blade receptacles](#)

Specifications and datasheets

[Eaton Specification Sheet - 4049-21BK-BU](#)

NEMA configuration

5-15R

Design type

Straight blade

Face/body material

Polypropylene base

Thermoset face

Receptacle type

Single



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)