

Eaton 4270BK

Catalog Number: 4270BK

Eaton residential grade duplex receptacle, #14-10 AWG, 15A, Commercial|Residential, Flush, 125V, Side and push, Black, Brass, High-impact thermoplastic, 5-15R, Duplex, Screw, Thermoplastic, Core pack



General specifications

Product Name	Catalog Number
Eaton residential grade duplex receptacle	4270BK
	UPC
	032664570520
Product Length/Depth	Product Height
1.31 in	4.19 in
Product Width	Product Weight
0.69 in	0.105 lb
Compliances	Certifications
RoHS Compliant	UL
NAFTA	NOM
	Federal Specification Classification 6233 01

defaultTaxonomyAttributeLabel

Device type

Receptacle

Type

Duplex receptacle

Amperage Rating

15A

Voltage rating

125V

Contact material

Brass

Features

No ears

Application

Commercial/residential

Device grade

Standard grade

Wiring method

Side and push

Number of wires

3

Mounting method

Flush

Number Of Poles

Two-pole

Style type

Standard

Material

Thermoplastic

Packaging type

Core pack

Color

Black

Connection type

Screw

Resources

Multimedia

[Residential straight blade receptacles](#)

Specifications and datasheets

[Eaton Specification Sheet - 4270BK](#)

[Duplex receptacles spec sheet](#)

Allowable wire size

#14-10 AWG

NEMA configuration

5-15R

Torque rating

14 lbf-inch

Design type

Straight blade

Face/body material

High-impact thermoplastic

Receptacle type

Duplex



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)