

Eaton 4560

Catalog Number: 4560

Eaton safety grip locking receptacle, #18-10 AWG, 15A, Industrial, 250V, Side wiring, Black, Brass, Single, L6-15, Two-pole, Three-wire, Nylon



General specifications

Product Name	Catalog Number
Eaton Arrow Hart locking receptacle	4560
UPC	Product Length/Depth
032664432705	6.5 in
Product Height	Product Width
1.5 in	3.5 in
Product Weight	Certifications
0.135 lb	Contact Manufacturer

defaultTaxonomyAttributeLabel

Special features

Safety grip locking receptacle

Type

Locking receptacle

Amperage Rating

15A

Voltage rating

250 V

Contact material

Brass

Application

Industrial

Device grade

Commercial

Wiring method

Side

Number of wires

3

Grounding

Number Of Poles

Two-pole

Color

Black

Material

Glass filled nylon

Operating temperature

-40 to 115 °C (-40 to 239 °F)

Allowable wire size

#18-10 AWG

NEMA configuration

L6-15

Design type

Single receptacle

Face/body material

Glass filled nylon

Resources

Brochures

[Wiring Devices Buyer's Guide](#)

Multimedia

[Arrow Hart - Connecting Safety to Reliability since 1890](#)

Specifications and datasheets

[Eaton Specification Sheet - 4560](#)

Receptacle type

Locking



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.
All other trademarks are property of their respective owners.



Eaton.com/socialmedia