

Eaton 5262CHB

Catalog Number: 5262CHB

Eaton Arrow Hart heavy duty industrial specification grade duplex receptacle, Auto-grounding,screw-catch, Half control, #14-10 AWG, 15A, Flush, 125V, Brown, Brass, High-impact nylon face,PVC base, 5-15R, Two-pole, Three-wire, Screw,



General specifications

Product Name	Catalog Number
Eaton Arrow Hart heavy-duty industrial specification grade duplex receptacle	5262CHB
	UPC
	032664744341
Product Length/Depth	Product Height
4.38 in	1.78 in
Product Width	Product Weight
1.91 in	0.22 lb

Certifications

NOM
Federal Specification Classification 6233
01
UL

defaultTaxonomyAttributeLabel

Device type

Receptacle

Type

Half control

Amperage Rating

15A

Voltage rating

125V

Contact material

Brass

Features

Auto-grounding

Half controlled

Application

Industrial

Device grade

Heavy-duty industrial specification grade

Wiring method

Back and side

Number of wires

Three-wire

Mounting method

Flush

Number Of Poles

Two-pole

Style type

Standard

Color

Brown

Connection type

Screw

Allowable wire size

#14-10 AWG

NEMA configuration

5-15R

Resources

Brochures

[Spec grade receptacles brochure](#)

[Controlled receptacles sell sheet](#)

Multimedia

[Residential straight blade receptacles](#)

Specifications and datasheets

[Eaton Specification Sheet - 5262CHB](#)

Design type

Straight blade

Face/body material

High-impact nylon face

PVC Base

Receptacle type

Duplex



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)