

Eaton 5284N

Catalog Number: 5284N

Eaton Arrow Hart extra heavy-duty industrial specification grade single receptacle, #14-10 AWG, 15A, Industrial, Panel, 125V, Back and side, Brown, Nickel-plated brass, Nylon, 5-15R, Single, Screw, Nylon, Core pack



General specifications

Product Name	Catalog Number
Eaton Arrow Hart extra heavy-duty industrial specification grade single receptacle	5284N
	UPC
	040893630243
Product Length/Depth	Product Height
1.32 in	3.28 in
Product Width	Product Weight
0.83 in	0.45 lb
Compliances	Certifications
RoHS Compliant	UL
	Federal Specification Classification 6233 01

defaultTaxonomyAttributeLabel

Device type

Receptacle

Type

Special use single receptacle

Amperage Rating

15A

Voltage rating

125V

Contact material

Nickel plated brass

Features

Short strap

Auto-grounding

Application

Industrial

Device grade

Extra heavy-duty industrial specification grade

Wiring method

Back and side

Number of wires

3

Mounting method

Panel

Number Of Poles

Two-pole

Style type

Special use panel mount

Material

Nylon

Packaging type

Core pack

Color

Brown

Connection type

Screw

Resources

Brochures

[Wiring Devices Buyer's Guide](#)

Multimedia

[Residential straight blade receptacles](#)

Specifications and datasheets

[Eaton Specification Sheet - 5284N](#)

Allowable wire size

#14-10 AWG

NEMA configuration

5-15R

Torque rating

14 lbf-inch

Design type

Straight blade

Face/body material

Nylon

Receptacle type

Single



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)