

# Eaton 5362BK

Catalog Number: 5362BK

Eaton Arrow Hart heavy-duty industrial specification grade duplex receptacle, #14-10 AWG, 20A, Industrial, Flush, 125V, Back and side, Black, Brass, Nylon, 5-20R, Duplex, Screw, Glass-filled nylon



## General specifications

Product Name	Catalog Number
Eaton Arrow Hart heavy-duty industrial specification grade duplex receptacle	5362BK
	UPC
	032664704383
Product Length/Depth	Product Height
4.38 in	1.78 in
Product Width	Product Weight
1.91 in	0.001 lb
Compliances	Certifications
RoHS Compliant	UL
NAFTA	NOM
	Federal Specification Classification 6233 01

## defaultTaxonomyAttributeLabel

### Device type

Receptacle

### Type

Duplex receptacle

### Amperage Rating

20A

### Voltage rating

125V

### Contact material

Brass

### Features

Auto-grounding

Screw-catch

### Application

Industrial

### Device grade

Heavy-duty industrial specification grade

### Wiring method

Back and side

### Number of wires

3

### Mounting method

Flush

### Number Of Poles

Two-pole

### Style type

Standard

### Material

Glass-filled nylon

### Color

Black

### Connection type

Screw

### Allowable wire size

#14-10 AWG

## Resources

### Brochures

[Spec grade receptacles brochure](#)

### Multimedia

[Residential straight blade receptacles](#)

### Specifications and datasheets

[Eaton Specification Sheet - 5362BK](#)

[Arrow Hart heavy-duty straight blade duplex receptacles](#)

NEMA configuration

5-20R

Torque rating

14 lbf-inch

Design type

Straight blade

Face/body material

Nylon

Receptacle type

Duplex



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)