

Eaton 5362CDV

Catalog Number: 5362CDV

Eaton Arrow Hart heavy duty industrial specification grade duplex receptacle, Auto-grounding, screw-catch, Dual control, #14-10 AWG, 20A, Flush, 125V, Ivory, Brass, High-impact nylon face, PVC base, 5-20R, 2-pole, 3-wire, Screw,



General specifications

Product Name	Catalog Number
Eaton Arrow Hart heavy-duty industrial specification grade duplex receptacle	5362CDV
	UPC
	032664744501
Product Length/Depth	Product Height
4.38 in	1.78 in
Product Width	Product Weight
1.91 in	0.22 lb

Certifications

Federal Specification Classification 6233
01
UL
NOM

defaultTaxonomyAttributeLabel

Device type

Receptacle

Type

Dual control

Amperage Rating

20A

Voltage rating

125V

Contact material

Brass

Features

Auto-grounding

Dual-controlled

Application

Industrial

Device grade

Heavy-duty industrial specification grade

Wiring method

Back and side

Number of wires

Three-wire

Mounting method

Flush

Number Of Poles

Two-pole

Style type

Standard

Material

Glass-filled nylon, PVC

Color

Ivory

Connection type

Screw

Allowable wire size

#14-10 AWG

Resources

Brochures

[Spec grade receptacles brochure](#)

[Controlled receptacles sell sheet](#)

Multimedia

[Residential straight blade receptacles](#)

Specifications and datasheets

[Eaton Specification Sheet - 5362CDV](#)

NEMA configuration

5-20R

Torque rating

14 lbf-inch

Design type

Straight blade

Face/body material

PVC Base

High-impact nylon face

Receptacle type

Duplex



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)