

Eaton 5362CDW

Catalog Number: 5362CDW

Eaton Arrow Hart heavy duty industrial specification grade duplex receptacle, Auto-grounding, screw-catch, Dual control, #14-10 AWG, 20A, Flush, 125V, White, Brass, High-impact nylon face, PVC base, 5-20R, 2-pole, 3-wire, Screw,



General specifications

Product Name	Catalog Number
Eaton Arrow Hart heavy-duty industrial specification grade duplex receptacle	5362CDW
	UPC
	032664744518
Product Length/Depth	Product Height
4.38 in	1.78 in
Product Width	Product Weight
1.91 in	0.22 lb

Certifications

Federal Specification Classification 6233
01
UL
NOM

defaultTaxonomyAttributeLabel

Device type

Receptacle

Type

Dual control

Amperage Rating

20A

Voltage rating

125V

Contact material

Brass

Features

Tamper resistant

Auto-grounding

Dual-controlled

Application

Industrial

Device grade

Heavy-duty industrial specification grade

Wiring method

Back and side

Number of wires

Three-wire

Mounting method

Flush

Number Of Poles

Two-pole

Style type

Standard

Material

Glass-filled nylon, PVC

Color

White

Connection type

Screw

Allowable wire size

Resources

Brochures

[Spec grade receptacles brochure](#)

[Controlled receptacles sell sheet](#)

Multimedia

[Residential straight blade receptacles](#)

Specifications and datasheets

[Eaton Specification Sheet - 5362CDW](#)

#14-10 AWG

NEMA configuration

5-20R

Torque rating

14 lbf-inch

Design type

Straight blade

Face/body material

High-impact nylon face

PVC Base

Receptacle type

Duplex



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia