

Eaton 5552-5EW

Catalog Number: 5552-5EW

Eaton Modular jacks and adapters, Coax type F insert adapter, Commercial, residential video applications, Flush, snap-in, White, Modular adapter, Coaxial type F jack, IDC termination, Thermoplastic, 0° to 40°C, RG-6, type F

General specifications



Product Name	Catalog Number
Eaton Modular jacks and adapters	5552-5EW
UPC	Product Length/Depth
032664627446	0.7 in
Product Height	Product Width
0.8 in	1.1 in
Product Weight	Compliances
0.026 lb	RoHS Compliant
Certifications	
cULus Listed	

defaultTaxonomyAttributeLabel

Device type

Coaxial type F jack

Type

Coax type F insert adapter

Application

Commercial, residential video applications

Wiring method

RG6

Mounting method

Snap-in

Flush

Cable type

RG-6, coaxial type F

Connector type

IDC termination

Material

Thermoplastic

Color

White

Design type

Modular adapter

Operating temperature

0 to 40 °C

Used with

For RG6 applications TV/satellite

Wire type

RG-6, type F

Resources

Catalogs

[Residential Buyers Guide D-04](#)

Specifications and datasheets

[Eaton Specification Sheet - 5552-5EW](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)