

# Eaton 5662W

Catalog Number: 5662W

Eaton Arrow Hart heavy-duty industrial specification grade duplex receptacle, #14-10 AWG, 15A, Industrial, Flush, 250V, Back and side, White, Brass, Impact-resistant nylon face, Glass-filled nylon base, 6-15R, Duplex, Screw, PVC, Core pack

## General specifications

Product Name	Catalog Number
Eaton Arrow Hart heavy-duty industrial specification grade duplex receptacle	5662W
	UPC
	032664643323

Product Length/Depth	Product Height
1.3 in	4.19 in

Product Width	Product Weight
0.87 in	0.25 lb

## Certifications

UL  
NOM  
Federal Specification Classification 6233  
01



## defaultTaxonomyAttributeLabel

### Device type

Receptacle

### Type

Duplex receptacle

### Amperage Rating

15A

### Voltage rating

250V

### Contact material

Brass

### Features

Compact design

Auto-grounding

### Application

Industrial

### Device grade

Heavy-duty industrial specification grade

### Wiring method

Back and side

### Number of wires

3

### Mounting method

Flush

### Number Of Poles

Two-pole

### Style type

Compact

### Material

PVC

### Packaging type

Core pack

### Color

White

### Connection type

Screw

## Resources

### Brochures

[Spec grade receptacles brochure](#)

### Multimedia

[Residential straight blade receptacles](#)

### Specifications and datasheets

[Eaton Specification Sheet - 5662W](#)

[Arrow Hart heavy-duty straight blade duplex receptacles](#)

Allowable wire size

#14-10 AWG

NEMA configuration

6-15R

Torque rating

14 lbf-inch

Design type

Straight blade

Face/body material

Impact-resistant nylon face

Glass-filled nylon base

Receptacle type

Duplex



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)