

Eaton 5879C

Catalog Number: 5879C

Eaton Arrow Hart straight blade flanged outlet , #18-10 AWG, 20A, Industrial, 250V, Back wire, Black and white, Brass, Nylon, 6-20R, Two-pole, three-wire, grounding, Clamp, Nylon, Core pack

General specifications



Product Name	Catalog Number
Eaton Arrow Hart straight blade flanged outlet	5879C
	UPC
	040893014418

Product Length/Depth	Product Height
3.1 in	4.6 in

Product Width	Product Weight
4.25 in	0.5 lb

Certifications

cULus Listed

Federal Specification Classification 6221

02



Powering Business Worldwide

defaultTaxonomyAttributeLabel

Device type

Flanged outlet

Type

Flanged outlet

Amperage Rating

20A

Voltage rating

250V

Contact material

Brass

Application

Industrial

Device grade

Heavy-duty industrial specification grade

Wiring method

Back wire

Number of wires

3

Number Of Poles

Two-pole

Style type

Flanged

Material

Nylon

Packaging type

Core pack

Color

White

Black

Connection type

Clamp

Allowable wire size

#18-10 AWG

NEMA configuration

6-20R

Resources

Multimedia

[Arrow Hart - Connecting Safety to Reliability since 1890](#)

Specifications and datasheets

[Eaton Specification Sheet - 5879C](#)

[Industrial Grade Straight Blade Devices Spec Sheet](#)

Torque rating

14 lbf-inch

Design type

Straight blade

Face/body material

Nylon

Receptacle type

Two-pole, three-wire, grounding



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia