

Eaton 6206CL

Catalog Number: 6206CL

Eaton Arrow Hart locking flanged outlet , Industrial, Two-pole,
Three-wire

General specifications



Product Name	Catalog Number
Eaton Arrow Hart locking flanged outlet	6206CL
UPC	Product Length/Depth
040893000305	2.875 in
Product Height	Product Width
2.18 in	2.062 in
Product Weight	Certifications
0.35 lb	cURus cRUus

defaultTaxonomyAttributeLabel

Special features

Lighting applications

Type

Locking flanged outlet

Amperage Rating

14A

Voltage rating

125-480 V

Contact material

Brass

Application

Industrial

Device grade

Extra heavy-duty industrial specification grade

Wiring method

Back

Number of wires

3

Grounding

Number Of Poles

Two-pole

Color

Gray

Material

Nylon

Operating temperature

-40 to 60 °C (-40 to 140 °F)

NEMA configuration

Non-NEMA

Torque rating

14-16 lbf-inch

Design type

Flanged outlet

Face/body material

Nylon

Resources

Brochures

Wiring Devices Buyer's Guide

Multimedia

Arrow Hart - Connecting Safety to Reliability since 1890

Specifications and datasheets

Eaton Specification Sheet - 6206CL



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)