

# Eaton 6252CDB

Catalog Number: 6252CDB

Eaton heavy-duty industrial specification grade decorator duplex receptacle, #14-10 AWG, 15A, Commercial, Flush, 125V, Back and side, Brown, Brass, High-impact nylon face, PVC base, 5-15R, Duplex, Screw, Nylon, PVC, Core pack



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton heavy-duty industrial specification grade decorator duplex receptacle	6252CDB
	<b>UPC</b>
	032664744747
<b>Product Length/Depth</b>	<b>Product Height</b>
1.32 in	4.19 in
<b>Product Width</b>	<b>Product Weight</b>
0.84 in	0.22 lb
<b>Compliances</b>	<b>Certifications</b>
RoHS Compliant	cULus Listed
NAFTA	Federal Specification Classification 6233 01

## defaultTaxonomyAttributeLabel

### Device type

Receptacle

### Type

Decorator duplex receptacle

### Amperage Rating

15A

### Voltage rating

125V

### Contact material

Brass

### Features

Dual controlled

Auto-grounding

Dual-controlled

### Application

Commercial

### Device grade

Heavy-duty industrial specification grade

### Wiring method

Back and side

### Number of wires

3

### Mounting method

Flush

### Number Of Poles

Two-pole

### Style type

Decorator

### Material

Nylon, PVC

### Packaging type

Core pack

### Color

Brown

### Connection type

## Resources

### Brochures

[Spec grade receptacles brochure](#)

[Controlled receptacles sell sheet](#)

### Multimedia

[Residential straight blade receptacles](#)

### Specifications and datasheets

[Eaton Specification Sheet - 6252CDB](#)

[Arrow Hart heavy-duty straight blade decorator receptacles](#)

Screw

Allowable wire size

#14-10 AWG

NEMA configuration

5-15R

Design type

Straight blade

Face/body material

PVC base

High-impact nylon face

Receptacle type

Duplex



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)