

# Eaton 6252CHBK

Catalog Number: 6252CHBK

Eaton commercial specification grade decorator duplex receptacle, Controlled, Half control, #14-10 AWG, 15A, Flush, 125V, Black, Brass, High-impact nylon face, PVC base, 5-15R, Two-pole, Three-wire, Screw, Nylon, PVC



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton heavy-duty industrial specification grade decorator duplex receptacle	6252CHBK
	<b>UPC</b>
	032664744815
<b>Product Length/Depth</b>	<b>Product Height</b>
4.38 in	1.78 in
<b>Product Width</b>	<b>Product Weight</b>
1.91 in	0.22 lb

## Certifications

cULus Listed  
Federal Specification Classification 6233  
01

## defaultTaxonomyAttributeLabel

### Device type

Receptacle

### Type

Half control

### Amperage Rating

15A

### Voltage rating

125V

### Contact material

Brass

### Features

Auto-grounding

Half controlled

### Application

Commercial

### Device grade

Commerical specification grade

### Wiring method

Back and side

### Number of wires

Three-wire

### Mounting method

Flush

### Number Of Poles

Two-pole

### Style type

Decorator

### Material

Nylon, PVC

### Color

Black

### Connection type

Screw

### Allowable wire size

#14-10 AWG

## Resources

### Brochures

[Spec grade receptacles brochure](#)

[Controlled receptacles sell sheet](#)

### Multimedia

[Residential straight blade receptacles](#)

### Specifications and datasheets

[Eaton Specification Sheet - 6252CHBK](#)

NEMA configuration

5-15R

Design type

Straight blade

Face/body material

High-impact nylon face

PVC Base

Receptacle type

Duplex



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)