

Eaton 6266HGC

Catalog Number: 6266HGC

Eaton Arrow Hart safety grip hospital grade straight blade plug, #18-12 AWG, 15A, Industrial, 125V, Back wire, Clear, Brass, Nylon, 5-15P, Two-pole, three-wire, grounding, Screw, Nylon, Core pack

General specifications



Product Name	Catalog Number
Eaton Arrow Hart safety grip hospital grade straight blade plug	6266HGC
	UPC
	040893052168
Product Length/Depth	Product Height
1.28 in	2.06 in
Product Width	Product Weight
1.46 in	0.201 lb
Compliances	Certifications
RoHS Compliant	cULus Listed
	Federal Specification Classification W-C-596F

defaultTaxonomyAttributeLabel

Device type

Plug

Type

Plug

Amperage Rating

15A

Voltage rating

125V

Contact material

Brass

Application

Industrial

Device grade

Extra heavy-duty hospital grade

Wiring method

Back wire

Number of wires

3

Number Of Poles

Two-pole

Style type

Straight body

Material

Nylon

Packaging type

Core pack

Color

Clear

Connection type

Screw

Allowable wire size

#18-12 AWG

NEMA configuration

5-15P

Resources

Brochures

[Wiring Devices Buyer's Guide](#)

Multimedia

[Arrow Hart - Connecting Safety to Reliability since 1890](#)

Specifications and datasheets

[Eaton Specification Sheet - 6266HGC](#)

Torque rating

14 lbf-inch

Design type

Straight blade

Face/body material

Nylon

Receptacle type

Two-pole, three-wire, grounding



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)