

# Eaton 6352CDW

Catalog Number: 6352CDW

Eaton commercial specification grade decorator duplex receptacle, Controlled, Dual control, #14-10 AWG, 20A, Panel, 125V, White, Brass, High-impact nylon face, PVC base, 5-20R, Two-pole, Three-wire, Screw, Nylon, PVC



## General specifications

Product Name	Catalog Number
Eaton heavy-duty industrial specification grade decorator duplex receptacle	6352CDW
	UPC
	032664744983

Product Length/Depth	Product Height
4.38 in	1.78 in

Product Width	Product Weight
1.91 in	0.22 lb

## Certifications

Federal Specification Classification 6233  
01  
cULus Listed

## defaultTaxonomyAttributeLabel

### Device type

Receptacle

### Type

Dual control

### Amperage Rating

20A

### Voltage rating

125V

### Contact material

Brass

### Features

Auto-grounding

Dual-controlled

### Application

Commercial

### Device grade

Commerical specification grade

### Wiring method

Back and side

### Number of wires

Three-wire

### Mounting method

Panel

### Number Of Poles

Two-pole

### Style type

Decorator

### Material

Nylon, PVC

### Color

White

### Connection type

Screw

### Allowable wire size

#14-10 AWG

## Resources

### Brochures

[Spec grade receptacles brochure](#)

[Controlled receptacles sell sheet](#)

### Multimedia

[Residential straight blade receptacles](#)

### Specifications and datasheets

[Eaton Specification Sheet - 6352CDW](#)

NEMA configuration

5-20R

Torque rating

14 lbf-inch

Design type

Straight blade

Face/body material

PVC Base

High-impact nylon face

Receptacle type

Duplex



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)