

# Eaton 6405BK

Catalog Number: 6405BK

Eaton safety grip locking flanged inlet, 20A, Commercial, 125/250V, Black, Single, Three-pole, Four-wire, Polycarbonate, 1.406 in

## General specifications



<b>Product Name</b>	<b>Catalog Number</b>
Eaton Arrow Hart locking flanged inlet	6405BK
<b>UPC</b>	<b>Product Length/Depth</b>
040893682457	3.06 in
<b>Product Height</b>	<b>Product Width</b>
2.19 in	2.19 in
<b>Product Weight</b>	<b>Certifications</b>
0.32 lb	UL Listed CSA certified

## defaultTaxonomyAttributeLabel

### Special features

Corrosion resistant locking receptacle

### Type

Locking flanged inlet

### Amperage Rating

20A

### Voltage rating

125/250 V

### Contact material

Brass

### Application

Industrial

### Device grade

Extra heavy-duty industrial specification grade

### Wiring method

Back

### Number of wires

Grounding

4

### Number Of Poles

Three-pole

### Color

Black

### Cutout

1.406 in

### Material

Nylon

### Operating temperature

-40 to 75 °C (-40 to 167 °F)

### Allowable wire size

#14-8 AWG

### NEMA configuration

L14-20

### Design type

Flanged inlet

## Resources

### Brochures

[Wiring Devices Buyer's Guide](#)

### Multimedia

[Arrow Hart - Connecting Safety to Reliability since 1890](#)

### Specifications and datasheets

[Eaton Specification Sheet - 6405BK](#)

Face/body material

Nylon



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)