

# Eaton 6450W

Catalog Number: 6450W

Eaton heavy-duty industrial specification grade decorator single receptacle, #14-10 AWG, 20A, Commercial, Flush, 250V, Back and side, White, Brass, Nylon, 5-20R, Single, Screw, Nylon, Core pack



## General specifications

Product Name	Catalog Number
Eaton heavy-duty industrial specification grade decorator single receptacle	6450W
	UPC 032664582233
Product Length/Depth	Product Height
1.32 in	4.19 in
Product Width	Product Weight
0.84 in	0.25 lb

## Certifications

UL  
Federal Specification Classification 6233  
01

## defaultTaxonomyAttributeLabel

### Device type

Receptacle

### Type

Decorator single receptacle

### Amperage Rating

20A

### Voltage rating

250V

### Contact material

Brass

### Features

Auto-grounding

### Application

Commercial

### Device grade

Heavy-duty industrial specification grade

### Wiring method

Back and side

### Number of wires

3

### Mounting method

Flush

### Number Of Poles

Two-pole

### Style type

Decorator

### Material

Nylon

### Packaging type

Core pack

### Color

White

### Connection type

Screw

### Allowable wire size

## Resources

### Brochures

[Spec grade receptacles brochure](#)

### Catalogs

[Arrow Hart Buyers Guide Section A](#)

### Multimedia

[Residential straight blade receptacles](#)

### Specifications and datasheets

[Eaton Specification Sheet - 6450W](#)

#14-10 AWG

NEMA configuration

5-20R

Torque rating

14 lbf-inch

Design type

Straight blade

Face/body material

Nylon

Receptacle type

Single



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)