

Eaton 67-2W-BU

Catalog Number: 67-2W-BU

Eaton panel mount/snap-in single receptacle, #14-12 AWG, 15A, Commercial, Snap-in, 125V, Quick Connect, White, Brass, Thermoset face and Polypropylene base, 5-15R, Single, Quick connect, Thermoplastic, Bulk



Photo is representative

General specifications

| | |
|---|-----------------------|
| Product Name | Catalog Number |
| Eaton panel mount/snap-in single receptacle | 67-2W-BU |
| | UPC |
| | 032664204609 |
| Product Length/Depth | Product Height |
| 0.94 in | 1.22 in |
| Product Width | Product Weight |
| 0.65 in | 0.06 lb |
| Certifications | |
| cRUus | |
| NOM | |
| Federal Specification Classification 6233 | |
| 01 | |

defaultTaxonomyAttributeLabel

Device type

Receptacle

Type

OEM

Amperage Rating

15A

Voltage rating

125V

Contact material

Brass

Features

Plastic back

Plastic clip

Application

Commercial

Device grade

Commercial specification grade

Wiring method

Quick connect

Number of wires

3

Mounting method

Snap-in

Number Of Poles

Two-pole

Style type

Snap-in, Rectangular

Material

Thermoplastic

Packaging type

Bulk

Color

White

Connection type

Quick connect

Resources

Catalogs

[Arrow Hart Buyers Guide A-22](#)

Multimedia

[Residential straight blade receptacles](#)

Specifications and datasheets

[Eaton Specification Sheet - 67-2W-BU](#)

Allowable wire size

#14-12 AWG

NEMA configuration

5-15R

Design type

Straight blade

Face/body material

Polypropylene base

Thermoset face

Receptacle type

Single



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)