

Eaton 6765HG

Catalog Number: 6765HG

Eaton Arrow Hart safety grip hospital grade straight blade angled plug, #18-12 AWG, 20A, Industrial, 125V, Back wire, Black and white, Brass, Nylon, 5-20P, Two-pole, three-wire, grounding, Screw, Nylon, 1-1/2", Core pack



General specifications

Product Name

Eaton Arrow Hart safety grip hospital grade straight blade angled plug

Catalog Number

6765HG

UPC

040893149141

Product Length/Depth

5.5 in

Product Height

2.25 in

Product Width

4.5 in

Product Weight

0.15 lb

Compliances

RoHS Compliant

Certifications

cULus Listed

Federal Specification Classification W-C-596F

cRUus

NOM

Federal Specification Classification 6233 01

defaultTaxonomyAttributeLabel

Device type

Plug

Type

Angled plug

Amperage Rating

20A

Voltage rating

125V

Contact material

Brass

Application

Industrial

Device grade

Extra heavy-duty hospital grade

Wiring method

Back wire

Number of wires

3

Number Of Poles

Two-pole

Style type

Angled body

Material

Nylon

Opening diameter

1-1/2"

Packaging type

Core pack

Color

Black

White

Connection type

Screw

Allowable wire size

#18-12 AWG

Resources

Catalogs

[Arrow Hart Buyers Guide B-08](#)

Multimedia

[Arrow Hart - Connecting Safety to Reliability since 1890](#)

Specifications and datasheets

[Eaton Specification Sheet - 6765HG](#)

NEMA configuration

5-20P

Torque rating

14 lbf-inch

Design type

Straight blade

Face/body material

Nylon

Receptacle type

Two-pole, three-wire, grounding



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)