

Eaton 6865HGC

Catalog Number: 6865HGC

Eaton Arrow Hart safety grip hospital grade straight blade angled plug, #18-12 AWG, 20A, Industrial, 125V, Back wire, Clear, Brass, Nylon, 6-20P, Two-pole, three-wire, grounding, Screw, Thermoplastic, Core pack

General specifications



Product Name	Catalog Number
Eaton Arrow Hart safety grip hospital grade straight blade angled plug	6865HGC
	UPC
	040893049182
Product Length/Depth	Product Height
2.38 in	3.75 in
Product Width	Product Weight
2.38 in	0.21 lb

Certifications

cULus Listed
Federal Specification Classification W-C-596F

defaultTaxonomyAttributeLabel

Device type

Plug

Type

Angled plug

Amperage Rating

20A

Voltage rating

125V

Contact material

Brass

Application

Industrial

Device grade

Extra heavy-duty hospital grade

Wiring method

Back wire

Number of wires

3

Number Of Poles

Two-pole

Style type

Angled body

Material

Thermoplastic

Packaging type

Core pack

Color

Clear

Connection type

Screw

Allowable wire size

#18-12 AWG

NEMA configuration

6-20P

Resources

Brochures

[Wiring Devices Buyer's Guide](#)

Multimedia

[Arrow Hart - Connecting Safety to Reliability since 1890](#)

Specifications and datasheets

[Eaton Specification Sheet - 6865HGC](#)

Torque rating

14 lbf-inch

Design type

Straight blade

Face/body material

Nylon

Receptacle type

Two-pole, three-wire, grounding



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)