

# Eaton 6882-SP

Catalog Number: 6882-SP

Eaton straight blade connector , #18-12 AWG, 15A, Residential, 125V, Back wire, Orange, Brass, Thermoplastic, 1-15R, Two-pole, two-wire, non grounding, Screw, 0.25-0.67", Thermoplastic, Retail Box



Photo is representative

## General specifications

Product Name	Catalog Number
Eaton straight blade connector	6882-SP
UPC	Product Length/Depth
032664490804	1.54 in
Product Height	Product Width
2.6 in	1.37 in
Product Weight	Certifications
0.11 lb	UL
	Federal Specification Classification 6221 02

## defaultTaxonomyAttributeLabel

### Device type

Connector

### Type

Connector

### Amperage Rating

15A

### Voltage rating

125V

### Contact material

Brass

### Application

Residential

### Device grade

Standard grade

### Wiring method

Back wire

### Number of wires

2

### Number Of Poles

Two-pole

### Style type

Straight body

### Cord range

0.25-0.67"

### Material

Thermoplastic

### Packaging type

Retail Box

### Color

Orange

### Connection type

Screw

### Allowable wire size

#18-12 AWG

## Resources

### Catalogs

[Residential Buyers Guide B-54](#)

### Multimedia

[Commercial and residential straight blade vinyl receptacles](#)

### Specifications and datasheets

[Eaton Specification Sheet - 6882-SP](#)

NEMA configuration

1-15R

Design type

Straight blade

Face/body material

Thermoplastic

Receptacle type

Two-pole, two-wire, non grounding



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)